



# ETS Mortuary Refrigerator (Side Open)

|                    |                   |                     |
|--------------------|-------------------|---------------------|
| Model              | No. of chamber(s) | Temperature Range   |
| <b>MOT 2B (SO)</b> | <b>2 nos.</b>     | <b>+2°C to +8°C</b> |



|                                 |   |
|---------------------------------|---|
| Safety Features & Certification | ISO 13485/IEC 61010-1/GDPMD ISO/IEC 17025                   |
| Dim. Ext. (mm) W x D x H        | 2550 x 1120 x 1960  |
| Dim. Int. (mm) W x D x H        | 2270 x 860 x 1220   |
| Internal & External Chamber     | Stainless Steel 304 (Int.: 0.9mm / Ext. 1.2mm)              |
| Stainless Steel Tray            | 600mm x 2000mm (SS 304)                                     |
| Temperature controller          | Microprocessor  |
| Door                            | Stainless Steel (2 nos.)                                    |
| Door Dimension (mm) L x H       | 2100 x 540  |
| Door Lock                       | Semi-recessed single pivoting x 2 nos.                      |
| Weight                          | 530KG   |
| Name Plate                      | 2 nos. (stainless steel)                                    |
| Panel Insulation                | High rigid polyurethane (100mm THK)                         |
| Density                         | 40KG/cu M ± 5%  |
| Voltage                         | 220V – 240V Single-phase 50Hz (13Amp plug)                  |
| Refrigerant                     | R407A   |
| Ambient Temperature             | +35°C   |
| Compressor                      | 3/4 HP  |
| Condensing Unit                 | Installed on top portion                                    |
| Lighting                        | 1 unit LED each chamber                                     |
| Cooling System                  | Forced-air fan x 3 (removable on top panel)                 |
| Defrost System                  | Auto-Off Circle Natural (built-in defrost heater for spare) |
| Light Switch                    | 1 each  |
| Evaporation of Condenser        | Using hot gas piping (NO drain water)                       |
| Alarm System                    | Hi/Low Alarm, Power Failure                                 |
| Remote Alarm Contact            | Dry Contact   |
| Castor                          | 6 nos. heavy duty   |

No. 32-G & 32-1, Dataran Mestika, Jalan Mawar 17, Taman Mestika, 56100 Kuala Lumpur, Malaysia.

Tel: +603 – 4292 2722 / 4288 2722 Fax: +603 – 4293 2722

Email: etsbiofr@gmail.com /info@etsbiofreeze.com Website: www.etsbiofreeze.com